

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200270127

Status:

Active

Overview:

Description:

Nano-Change (M8) Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 0.25mm² PVC Cable, 2.0m (6.56') Length

Agency Certification	
UL	E152210
General	
Product Family	Industrial Cordsets
Series	120027
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	nanochange_40m841_products
Product Name	Nano-Change (M8)
Protocol	N/A
Region	Europe
Type	Single Ended
UPC	883906026349
Physical	
Cable Diameter	5.08mm (.200")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	69.861/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-25°C to +80°C
Wire Size AWG	N/A
Wire/Cable Type	UL 2464
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	60V
Material Info	
Engineering Number	404000E02M020
Reference - Drawing Numbers	
Sales Drawing	1200860594-000

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)4578-DC (25 June 2020)

Lead

Halogen-Free Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS ELV

50 Image Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

120027 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION