

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200652261](#)
Status: **Active**
Overview:
Description: Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 3 Poles, Female (90°) to Pigtail, 22 AWG, Unshielded WSOR Cable, 5.0m (16.40') Length

Agency Certification	
UL	E152210
General	
Product Family	Industrial Cordsets
Series	120065
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Brass
Overview	brad_m8_and_microchange_m12_cordsets_with_knurled_hexnuts_and_wsor_cable
Product Name	Micro-Change (M12)
Protocol	N/A
Region	Europe
Type	Single Ended
UPC	887191554754
Physical	
Cable Diameter	4.80mm (.189")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	141.000/g
Orientation	90° to Pigtail
Poles	3
Temperature Range - Operating	-25°C to +85°C
Wire Size AWG	22
Wire/Cable Type	WSOR
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	250V
Material Info	
Engineering Number	803001B30M050
Reference - Drawing Numbers	
Sales Drawing	SD-120065-076-001

EU ELV
Compliant with Exemption 3

EU RoHS
Compliant with Exemption 6(c)
REACH SVHC
Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead
Halogen-Free
Status
Not Relevant
For more information, please visit [Contact US](#)
[hexnuts_and_wsor_cable](#)

China RoHS

China ROHS	Not Relevant
ELV	Compliant with Exemption 3
RoHS Phthalates	Not Contained

Search Parts in this Series
[120065](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION