

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200658573

Status:


Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

Micro-Change (M12) Single-Ended Cordset, 5 Poles, Female (90°) to Pigtail, 0.34mm² PVC Cable, 1.0m (3.28') Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E152210

General

Product Family

Series

Connector End A

Connector End B

IP Rating

Material - Contact

Overview

Product Name

Protocol

Region

Type

UPC

Industrial Cordsets

120065

Micro-Change (M12)

Pigtail

IP67

Copper Alloy

Brad Micro-Change (M12) Connectors

Micro-Change (M12)

N/A

Europe

Single Ended

78172514393

Physical

Cable Diameter

Cable Length

Color - Cable Jacket

Coupling Style

Gender

Keyway

LED Indicator

Material - Cable Jacket

Material - Connector Body

Material - Coupling Nut

Material - O-Ring

Material - Plating Mating

Net Weight

Orientation

Poles

Temperature Range - Operating

Wire Size AWG

Wire/Cable Type

5.80mm (.230")

1.0m (3.28')

Black

Threaded

Female-Pigtail

Single

No

PVC

PUR

Nickel-plated Brass

Fluoro-elastomer

Gold

67.095/g

90° to Pigtail

5

-30°C TO +80°C

N/A

UL 2464

Electrical

Current - Maximum per Contact

Voltage - Maximum

4.0A

250V AC/DC

Material Info

Engineering Number

805001E03M010

Reference - Drawing Numbers

Sales Drawing

1200658573-000

EU ELV

Not Relevant

EU RoHS

Compliant with
Exemption 6(c)

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

120065 Series

This document was generated on 08/17/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION