

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200720250

Status:

Active

Overview:

Brad Micro-Change (M12) Connectors

Description:


Micro-Change (1/2"-20 UNF) Single-Ended Cordset, 3 Poles, Female (90°) to Pigtail, 22 AWG, PVC Cable, 1.83m (6.0') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
UL	E152210
General	
Product Family	Industrial Cordsets
Series	120072
Connector End A	Micro-Change (1/2" - 20 UNF)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (1/2" - 20 UNF)
Protocol	PROFIBUS
Region	America
Type	Single Ended
UPC	78678875912
Physical	
Cable Diameter	5.72mm (.225")
Cable Length	1.83m (6.0')
Color - Cable Jacket	Yellow
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Dual
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - O-Ring	Nitrile Rubber
Material - Plating Mating	Gold
Net Weight	98.883/g
Orientation	90° to Pigtail
Poles	3
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	22
Wire/Cable Type	UL 2661
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC
Material Info	
Engineering Number	703001D02F060
Reference - Drawing Numbers	
Sales Drawing	SD-120072-010-001



EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

120072 Series

This document was generated on 07/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION