

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200845109

Status:

Active

Overview:

Description:

Ultra-Lock (M12) Receptacle, 5 Poles, PG9 Mounting Threads, Male (Straight) to 0.34mm² PVC Leads, 0.30m (11.81") Length

General

Product Family

Industrial Receptacles

Series

120084

IP Rating

IP69K

NEMA Rating

NEMA 6

Overview

ultralock_connection_system

Product Name

Ultra-Lock (M12)

Type

Single Ended (pigtail)

UPC

883906778927

Physical

Coupling Type

External Thread

Gender

Male

Keyway

Single

Length

0.30m

Material - Component

Nickel-plated Brass

Mounting Thread Size

PG9

Net Weight

23.586/g

Orientation

Straight

Panel Mount

Front

Poles

5

Temperature Range - Operating

-25° to +90°C

Wire Size AWG

22

Wire/Cable Type

UL 1569

Electrical

Current - Maximum per Contact

4.0A

Voltage - Maximum

60V

Material Info

Engineering Number

WR5J26E03C3003

Reference - Drawing Numbers

Sales Drawing

SD-120084-026-001

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2021)4569-DC (8 July 2021)

Lead

Halogen-Free Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

120084 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION