

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200905073](#)
Status: **Active**
Overview: [Brad Nano-Change \(M8\) Products](#)
Description: Nano-Change (M8) Receptacle, M8 x 1.0 Mounting Threads, Male (Straight) to Leads, 0.20m (7.87") Length, Back Mount, with 3 Poles on Mating Side

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family Industrial Receptacles
Series [120090](#)
IP Rating IP67
NEMA Rating NEMA 6
Overview [Brad Nano-Change \(M8\) Products](#)
Product Name Nano-Change (M8)
Type Single Ended (pigtail)
UPC 883906784508

Physical

Coupling Type External Thread
Gender Male
Keyway None
Length 0.20m
Material - Component Nickel-plated Brass
Mounting Thread Size M8 x 1.0
Net Weight 66.000/g
Orientation Straight
Panel Mount Back
Poles 3
Temperature Range - Operating -25°C to +90°C
Wire Size AWG 24
Wire/Cable Type Leads

Electrical

Current - Maximum per Contact 4.0A
Voltage - Maximum 60V AC / 75V DC

Material Info

Engineering Number 4R3F46E02C200

Reference - Drawing Numbers

Sales Drawing SD-120090-004



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - ED/01/2018 (15 January 2018)
Bisphenol-A

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[120090](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION