

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1300540021

Status: **Active**

Overview: Brad Industrial Ethernet Solutions

Description: Ultra-Lock (M12) D-Coded to RJ-45 Adapter, Straight to Straight, 4 PoleFemale to RJ45 Male, 2.0m (6.56') Length

Documents:

Drawing (PDF)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E200650

General

Product Family	Industrial Receptacles
Series	<u>130054</u>
IP Rating	IP67
Overview	<u>Brad Industrial Ethernet Solutions</u>
Product Name	RJ45, Ultra-Lock (M12)
Type	Adapter
UPC	78678804234

Physical

Coupling Type	Push to Lock
Gender	Female-Male
Keyway	D-coded
Length	2.0m
Material - Component	Nylon
Mounting Thread Size	N/A
Net Weight	115.212/g
Orientation	Straight
Panel Mount	N/A
Poles	4
Temperature Range - Operating	N/A
Wire Size AWG	N/A
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	N/A

Material Info

Engineering Number ERWPAB3002M020

Reference - Drawing Numbers

Sales Drawing SD-130054-002-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

130054 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION