

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1727040031

Status: **Active**

Overview: FCT D-Sub Connectors


Description: FCT Mixed Layout D-Sub Housing, Male, Tin-plated Shell with Dimples, 3 Circuits

Documents:

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Brochure (PDF)



Series image - Reference only

General

Product Family	D-Sub Products
Series	<u>172704</u>
IP Rating	IP20
Overview	<u>FCT D-Sub Connectors</u>
Product Category	D-Sub Connector
Product Name	FCT Products
Type	Mixed Layout
UPC	889056019422

Physical

Circuits (Loaded)	0
Circuits (maximum)	3
Color - Resin	Green
Gender	Male
Material - Resin	PBT
Material - Shell	Steel
Net Weight	5.500/g
Number of Rows	1
PCB Locator	No
PCB Retention	None
Packaging Type	Carton
Panel Mount	Rear
Panel Mount Method	Flange
Plating - Shell	Tin
Polarized to Mating Part	Yes
Ports	1
Shielded	Yes
Temperature Range - Operating	-55° to +130°C
Waterproof / Dustproof	No
Waterproof / Dustproof Type	IP20

Material Info

Engineering Number FM3W3P-K120

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

172704 Series

Mates With

FCT Mixed Layout D-Sub, Size 2, 3W3,
Socket

Use With

FCT Coaxial, High Power, High Voltage, or Pneumatic Contacts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION