

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION


Part Number: [1727040032](#)
Status: **Active**
Overview: [FCT D-Sub Connectors](#)
Description: FCT Mixed Layout D-Sub Housing, Female, Tin-plated Shell without Dimples, 3 Circuits

Documents:
[Datasheet \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

General
Product Family D-Sub Products
Series [172704](#)
IP Rating IP20
Overview [FCT D-Sub Connectors](#)
Product Category D-Sub Connector
Product Name FCT Products
Type Mixed Layout
UPC 889056019439

Physical
Circuits (Loaded) 0
Circuits (maximum) 3
Color - Resin Green
Gender Female
Material - Resin PBT
Material - Shell Steel
Net Weight 5.900/g
Number of Rows 1
PCB Locator No
PCB Retention None
Packaging Type Carton
Panel Mount Rear
Panel Mount Method Flange
Plating - Shell Tin
Polarized to Mating Part Yes
Ports 1
Shielded Yes
Temperature Range - Operating -55° to +130°C
Waterproof / Dustproof No
Waterproof / Dustproof Type IP20

Material Info
Engineering Number FM3W3S-K121



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[172704](#) Series

Mates With
FCT Mixed Layout D-Sub, Size 2, 3W3, Plug

Use With
FCT Coaxial, High Power, High Voltage, or Pneumatic Contacts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION