

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION


Part Number: 1727040041
Status: Active
Overview: FCT D-Sub Connectors
Description: FCT Mixed Layout D-Sub Housing, Male, Tin-plated Shell with Dimples, Polarized, 2 Circuits

Documents:
[Datasheet \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

General
Product Family D-Sub Products
Series 172704
IP Rating IP20
Overview FCT D-Sub Connectors
Product Category D-Sub Connector
Product Name FCT Products
Type Mixed Layout
UPC 889056019521

Physical
Circuits (Loaded) 0
Circuits (maximum) 2
Color - Resin Black
Gender Male
Material - Resin PBT
Material - Shell Steel
Net Weight 4.300/g
Number of Rows 1
PCB Locator No
PCB Retention None
Packaging Type Carton
Panel Mount Rear
Panel Mount Method Flange
Plating - Shell Tin
Polarized to Mating Part Yes
Ports 1
Shielded Yes
Temperature Range - Operating -55° to +130°C
Waterproof / Dustproof No
Waterproof / Dustproof Type IP20

Material Info
Engineering Number F2W2PC-K120



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)4578-DC (25 June 2020)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
172704 Series

Mates With
FCT Mixed Layout D-Sub, Size 1, 2W2SC, Socket

Use With
FCT Coaxial, High Power, High Voltage, or Pneumatic Contacts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION