

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1727040042

Status:

Active

Overview:

FCT D-Sub Connectors

Description:

FCT Mixed Layout D-Sub Housing, Female, Tin-plated Shell without Dimples, Polarized, 2 Circuits

Documents:

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Brochure (PDF)

General

Product Family

D-Sub Products

Series

172704

IP Rating

IP20

Overview

FCT D-Sub Connectors

Product Category

D-Sub Connector

Product Name

FCT Products

Type

Mixed Layout

UPC

889056019538

Physical

Circuits (Loaded)

0

Circuits (maximum)

2

Color - Resin

Black

Gender

Female

Material - Resin

PBT

Material - Shell

Steel

Net Weight

4.000/g

Number of Rows

1

PCB Locator

No

PCB Retention

None

Packaging Type

Carton

Panel Mount

Rear

Panel Mount Method

Flange

Plating - Shell

Tin

Polarized to Mating Part

Yes

Ports

1

Shielded

Yes

Temperature Range - Operating

-55° to +130°C

Waterproof / Dustproof

No


Waterproof / Dustproof Type

IP20

Material Info

Engineering Number

F2W2SC-K121



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

172704 Series

Mates With

FCT Mixed Layout D-Sub, Size 1, 2W2PC, Plug

Use With

FCT Coaxial, High Power, High Voltage, or Pneumatic Contacts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION