

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1731120228](#)
Status: **Active**
Overview: [FCT D-Sub Connectors](#)
Description: FCT Machined Contact, Female, Crimp, 1.30µm Gold Plating, Split Tine, 22-28 AWG

Documents:
[Datasheet \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

General
Product Family D-Sub Products
Series [173112](#)
Contact Type Machined Crimp
Overview [FCT D-Sub Connectors](#)
Product Category Contacts
Product Name FCT Products
Type High Density
UPC 889056489836

Physical
Durability (mating cycles max) 500
Gender Female
Material - Contact Brass
Net Weight 0.200/g
Orientation Straight
Packaging Type Bag
Plating - Contact Gold over Nickel
Plating min - Mating 1.300µm
Plating min - Termination 1.300µm
Temperature Range - Operating -55° to +130°C
Termination Style Crimp
Wire Size AWG 22, 24, 26, 28

Electrical
Current - Maximum per Contact 5.0A

Material Info
Engineering Number FK22SL-13V-5783

Reference - Drawing Numbers
Sales Drawing 1731120223-000



EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - ED/71/2019 (16 July 2019)	
lead	
Halogen-Free Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[173112](#) Series

Use With
FCT High-Density Connectors

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION