

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190030011

Status:

Active

Overview:

Standard Quick-Disconnect Terminals

Description:

InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²), Bag, Tab 4.75 x 0.51mm, Salmon

Documents:

3D Model (PDF)

Drawing (PDF)

3D Model

Product Specification PS-19902-008-001 (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR18689

E79133

General

Product Family

Series

Comments

Crimp Quality Equipment

Insulated

Overview

Product Name

Taxonomy

Type

UPC

Quick Disconnects

19003

Funnel Entry

Yes

Fully

Standard Quick-Disconnect Terminals

InsulKrimp

Quick Disconnects

Quick Disconnect

800753028487

Physical

Barrel Type

Color - Resin

Flammability

Gender

Glow-Wire Capable

Insulation

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Orientation

Packaging Type

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Tab Thickness

Tab Width

Temperature Range - Operating

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Closed

Salmon

94V-2

Female

No

Nylon (PA)

None

Brass

Tin

Tin

Nylon

0.600/g

Straight

Bag

4.064µm

4.064µm

No

0.51mm

4.75mm

-65° to +105°C

Crimp or Compression

3.43mm max.

18, 20, 22

Electrical

Voltage - Maximum

600V

Solder Process Data

Lead-freeProcess Capability

N/A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19003 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade Hand Crimp Tool for InsulKrimp Quick Disconnect Terminals, 10-22 AWG	640010400
Crimp Head for the AT-200 Pneumatic Hand Tool	640050400

Material Info

Engineering Number AA-2202

Reference - Drawing Numbers

Product Specification PS-19902-008-001, PS-19902-011-001,
PS-19902-013-001
Sales Drawing SD-19003-005-001

This document was generated on 01/31/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION