


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022013077](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: KK 254 Crimp Housing, Friction Ramp with Polarizing Ribs, 7 Circuits, Natural



Documents:
[3D Model](#) [Packaging Specification 26950002-PK-000 \(PDF\)](#)
[Drawing \(PDF\)](#) [Test Summary TS-10-07-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-10-07-001 \(PDF\)](#)

Agency Certification
CSA LR19980
UL E29179

General
Product Family Crimp Housings
Series [2695](#)
Application Signal, Wire-to-Board
Overview [KK Interconnect Solutions](#)
Product Name KK 254
UPC 800753593879

Physical
Circuits (maximum) 7
Color - Resin Natural (White)
Flammability 94V-0
Gender Receptacle
Glow-Wire Capable No
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 0.920/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.54mm
Pitch - Termination Interface 2.54mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating See Product Specification

Solder Process Data
Lead-freeProcess Capability N/A

Material Info
Engineering Number 2695-07RP

Reference - Drawing Numbers
Packaging Specification 26950002-PK-000
Product Specification PS-10-07-001
Sales Drawing 26950000-SD-000
Test Summary TS-10-07-001

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2020)9139-DC (19
Jan 2021)
Halogen-Free
Status
Low-Halogen
For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
[2695 Series](#)

Mates With
KK254 PCB Headers [42375](#) , [42377](#) , [42376](#)
 , [4030](#) , [6373](#) , [6410](#) , [171856](#) , [171857](#)

Use With
KK Crimp Terminals [2759](#) , [6459](#) , [41572](#)
 , [4809](#) , [8088](#)
 KK 254 Pre-Crimped
Leads [797580007](#) , [797580015](#)