

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2451320605](#)
Status: **Active**
Overview: [Micro-Fit Connector System](#)
Description: Micro-fit 3.0-to-Micro-Fit 3.0 Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, 0.5m Length, 6 Circuits, Black

Documents:

3D Model	Packaging Specification 2014400104-PK (PDF)
3D Model (PDF)	Datasheet (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Cable Assemblies
Series	245132
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Micro-Fit 3.0 Both Ends
Overmolded	Yes
Overview	Micro-Fit Connector System
Product Name	Micro-Fit 3.0
Type	Overmolded Assembly
UPC	889056853835

Physical

Cable Length	0.50m
Circuits (Loaded)	6
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	39.200/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	3.00mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	5.50mm
Wire Size AWG	20
Wire/Cable Type	UL 2464

Electrical

Current - Maximum per Contact	5.6A
Voltage - Maximum	300V AC

Material Info

Reference - Drawing Numbers

Packaging Specification	2014400104-PK
Sales Drawing	2014400091-000



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[245132](#) Series

Mates With

Micro-Fit 3.0 Plug Housings [43020](#)

Micro-Fit 3.0 Headers [43045](#)
Micro-Fit 3.0 Test Plug [44242](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION