

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0026034121](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: KK 3.96mm Crimp Terminal Housing, Use With Trifurcon Terminals, Friction Ramp, 12 Circuits, Natural
Replacement Part Number : <http://www.molex.com/molex/search/partSearch?pQuery=&sType=p&query=000950812109508121> (see comments)

Documents:
[3D Model](#) [Product Specification PS-40-02-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification
CSA LR19980

General
Product Family Crimp Housings
Series [6442](#)
Application Power, Wire-to-Board
Comments Replacement is V-0 instead of V-2
Overview [KK Interconnect Solutions](#)
Product Name KK 396
Replacement Part Number [09508121](#) (see comments)
UPC 800753587076

Physical
Circuits (maximum) 12
Color - Resin Natural
Flammability 94V-2
Gender Receptacle
Glow-Wire Capable No
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 3.192/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 3.96mm
Stackable No
Temperature Range - Operating See Product Specification

Solder Process Data
Lead-freeProcess Capability N/A

Material Info
Engineering Number 6442-R12-Z

Reference - Drawing Numbers
Product Specification PS-40-02-001
Sales Drawing SD-6442



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per - D(2020)9139-DC (19 Jan 2021)
Halogen-Free Status
Low-Halogen
For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
[6442](#) Series

Mates With
3.96mm Pitch KK Crimp Terminal Housing
Use with Trifurcon Terminals, Friction Ramp, 12 Circuits

Use With
MarKK Crimp Terminals [45570](#)
KK Trifurcon Crimp Terminals [6838](#) , [7258](#)
L1NK 396 Pre-Crimped Lead [797582145](#) , [797582146](#)