

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348242244](#)
Status: **Active**
Overview: [Mini50 Connection Systems](#)
Description: Mini50 Unsealed Receptacle, Dual Row, Bridged, with CPA, 24 Circuits, EcoPaXX Resin, Polarization Option A, Black

Documents:

3D Model	Application Specification AS-34791-020-CH-001 (PDF)
3D Model (PDF)	Packaging Specification PK-31301-538-001 (PDF)
Drawing (PDF)	Test Summary 347910020-TS-000 (PDF)
Product Specification PS-34791-020-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-34791-020-001 (PDF)	Product Literature (PDF)

General

Product Family	Crimp Housings
Series	34824
Application	Automotive, Power, Wire-to-Board
Overview	Mini50 Connection Systems
Polarization	A
Product Name	Mini50
UPC	191128232623

Physical

Circuits (maximum)	24
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	4.273/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification	AS-34791-020-001, AS-34791-020-CH-001
Packaging Specification	PK-31301-538-001
Product Specification	PS-34791-020-001
Sales Drawing	SD-34824-002-001, SD-34824-003-001
Test Summary	347910020-TS-000



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[34824](#) Series

Mates With

Mini50 Vertical Headers [34825](#) , Mini50
Right-Angle Through Hole Header [34826](#) ,
Mini50 Right-Angle Surface Mount Header
[34897](#)

Use With

CTX50 Unsealed Terminals [560023](#)