

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0039013048](#)
Status: **Active**
Overview: [Mini-Fit Family Power Connectors](#)
Description: [Mini-Fit Jr. Receptacle Housing, Dual Row, 4 Circuits, UL 94V-0, Natural](#)

Documents:

3D Model	Product Specification PS-5556-002-001 (PDF)
3D Model (PDF)	Application Specification 55560001-AS-000 (PDF)
Drawing (PDF)	Application Specification AS-5557-001-001 (PDF)
Product Specification 55560002-PS-CH-000 (PDF)	Packaging Specification PK-5557-002-000 (PDF)
Product Specification 55560002-PS-ES-000 (PDF)	Test Summary 55560010-TS-000 (PDF)
Product Specification 55560002-PS-SK-000 (PDF)	Test Summary TS-5556-002-001 (PDF)
Product Specification PS-45750-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-5556-001-001 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	5557
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current derating information.. See Molex product specification Mini-Fit Family Power Connectors
Overview	
Product Name	Mini-Fit Jr.
UPC	800754943208

Physical

Breakaway	No
Circuits (maximum)	4
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.120/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Electrical

Current - Maximum per Contact	13.0A
-------------------------------	-------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----



Series image - Reference only

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

China RoHS

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free
Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS
ELV

Green Image
Compliant
Not Contained

Search Parts in this Series
[5557](#) Series

Mates With

[39012046](#) Panel Mount Plug, [39013049](#)
Free Hanging Plug, [5566](#) Vertical Headers,
[5569](#) Right Angle Headers, [42440](#) PCB
Headers

Use With

[5556](#) Mini-Fit Female Crimp Terminals,
[45750](#) Mini-Fit Plus HCS Crimp Terminal

Material Info

Engineering Number 5557-04R1-210

Reference - Drawing Numbers

Application Specification 55560001-AS-000, AS-5557-001-001
Packaging Specification PK-5557-002-000
Product Specification 55560002-PS-CH-000, 55560002-PS-ES-000,
55560002-PS-SK-000, PS-45750-001-001,
PS-5556-001-001, PS-5556-002-001
Sales Drawing 55570001-SD-000
Test Summary 55560010-TS-000, TS-5556-002-001

This document was generated on 08/16/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION