

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0436450210](#)
Status: **Active**
Overview:
Description: Micro-Fit 3.0 Receptacle Housing, Single Row, 2 Circuits, UL 94V-2, Glow-Wire Capable, Black

Agency Certification

CSA LR19980

General

Product Family Crimp Housings
Series [43645](#)
Application Power, Wire-to-Board, Wire-to-Wire
Overview microfit_30
Product Name Micro-Fit 3.0
UPC 889056720007

Physical

Circuits (maximum) 2
Color - Resin Black
Flammability 94V-2
Gender Receptacle
Glow-Wire Capable Yes
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 0.290/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 3.00mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification 430250000-AS-000
Packaging Specification PK-43645-001-001
Product Specification 436500001-PS-JA-000, 436500001-PS-KO-000,
436500001-PS-SP-000, PS-43650-001
Sales Drawing SD-43645-002-001
Test Summary 430450005-TS-000, 430450006-TS-000,
TS-43045-001-001, TS-43045-002-001,
TS-43045-003-001, TS-46235-001-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[43645](#) Series

Mates With

Micro-Fit 3.0 Plug Housings [43640](#)

Micro-Fit TPA Plug Housing [200875](#)

Micro-Fit 3.0 Headers [43650](#)

Micro-Fit 3.0 Cable Assembly [214752](#) ,
[214753](#)

Use With

Micro-Fit 3.0 Female Crimp Terminals
[43030](#)
 Micro-Fit RMF Female Crimp
Terminals [46235](#)
Micro-Fit 3.0 Pre-
Crimped Leads [797580002](#) , [797580004](#) ,
[797580010](#) , [797580012](#) , [214760](#) , [214761](#)