

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0050291662](#)
Status: **Active**
Overview: Mini-Fit Family Power Connectors
Description: Mini-Fit Jr. Receptacle Housing, Single Row, PA Polyamide Nylon 6/6, UL 94V-2, 3 Circuits, Positive Latch, First Mate/Last Break, Glow-Wire Capable, Black

Documents:

3D Model	Packaging Specification PK-5557-002-000 (PDF)
Drawing (PDF)	Test Summary 457500003-TS-000 (PDF)
3D Model (PDF)	Test Summary 55560010-TS-000 (PDF)
Product Specification PS-45750-001-001 (PDF)	Test Summary TS-5556-002-001 (PDF)
Product Specification PS-5556-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 55560001-AS-000 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	46994
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current derating information.
Overview	Mini-Fit Family Power Connectors
Product Name	Mini-Fit Jr.
UPC	822348516322

Physical

Breakaway	No
Circuits (maximum)	3
Color - Resin	Black
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.950/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +105°C

Electrical

Current - Maximum per Contact	13.0A
-------------------------------	-------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[46994](#) Series

Mates With

[172646](#) Crimp Housings Plug, [172647](#) PCB Header, [172648](#) PCB Header

Use With

Mini-Fit Female Crimp Terminals [5556](#)

Mini-Fit Plus Female Crimp Terminals [45750](#)

Material Info

Engineering Number 46994-0312

Reference - Drawing Numbers

Application Specification 55560001-AS-000
Packaging Specification PK-5557-002-000
Product Specification PS-45750-001-001, PS-5556-001-001
Sales Drawing SD-46994-0001
Test Summary 457500003-TS-000, 55560010-TS-000,
TS-5556-002-001

This document was generated on 06/25/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION