

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0050375083

Status:


Active

Overview:

Mini-SPOX Wire-to-Board Connector System

Description:

2.50mm Pitch, Mini-SPOX Receptacle Crimp Housing, Single Row, Friction Lock, 8 Circuits, Natural



Documents:	
Drawing (PDF)	Product Specification 52641001-PS-000 (PDF)
3D Model (PDF)	Product Specification PS-5264-001-001 (PDF)
3D Model	Packaging Specification SPK-5264-001-001 (PDF)
2D Drawing DXF (PDF)	RoHS Certificate of Compliance (PDF)
2D Drawing (DXF)	

Agency Certification	
UL	E29179
General	
Product Family	Crimp Housings
Series	5264
Application	Signal, Wire-to-Board
Overview	Mini-SPOX Wire-to-Board Connector System
Product Name	Mini-SPOX
UPC	800753578388
Physical	
Circuits (maximum)	8
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	436.100/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Material Info	
Engineering Number	5264-08
Reference - Drawing Numbers	
Packaging Specification	SPK-5264-001-001
Product Specification	52641001-PS-000, PS-5264-001-001
Sales Drawing	52640001-SD-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

5264 Series

Mates With

Mini-SPOX Vertical Header [5267](#) . Mini-SPOX Right-Angle Header [5268](#)

Use With

Mini-SPOX Receptacle Terminal [5263](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION