

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5037630491](#)
Status: **Active**
Overview: [Pico-Lock Connector System](#)
Description: 1.00mm Pitch, Pico-Lock PCB Header, Single Row, Right-Angle, Surface Mount, Gold over Nickel Plating, Positive Lock, 4 Circuits, Tape and Reel

Documents:

3D Model	Application Specification AS-503764-001-001 (PDF)
3D Model (PDF)	Packaging Specification SPK-503763-001-001 (PDF)
Drawing (PDF)	Datasheet (PDF)
Product Specification 5037641001-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-503764-001-001 (PDF)	

Agency Certification

UL	E29179
----	--------

General

Product Family	PCB Headers
Series	503763
Application	Signal, Wire-to-Board
Overview	Pico-Lock Connector System
Product Name	Pico-Lock
UPC	887191353838

Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	SC-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	N/A
Lock to Mating Part	Yes
Mated Height	1.50mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Resin	High Temperature Thermoplastic
Net Weight	76.240/mg
Number of Rows	1
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.100µm
Polarized to Mating Part	Yes
Shrouded	Yes
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	150V AC (RMS)/DC



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[503763](#) Series

Mates With

Pico-Lock Crimp Housing [503764](#)
Pico-Lock Cable Assembly [15131](#)

Material Info

Reference - Drawing Numbers

Application Specification	AS-503764-001-001
Packaging Specification	SPK-503763-001-001
Product Specification	5037641001-PS-000, PS-503764-001-001
Sales Drawing	5037630000-SD-000

This document was generated on 08/23/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION