

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5055650201

Status:

Active

Overview:

Description:

1.25mm Pitch, Micro-Lock Plus Receptacle Crimp Housing, Single Row, Positive Lock, 2 Circuits, Black

Agency Certification	
UL	E29179
General	
Product Family	Crimp Housings
Series	505565
Application	Signal, Wire-to-Board
Overview	microlock_plus_wiretoboard_connector_system
Product Name	Micro-Lock Plus
UPC	889056502900
Physical	
Circuits (maximum)	2
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	67.955/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-505565-001-001
Packaging Specification	5055659200-200
Product Specification	5055650000-000, 5055650002-000, 5055651000-PS-000, 5055651002-PS-000
Sales Drawing	5055650002-SD-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

505565 Series

Mates With

Micro-Lock Plus Vertical Header [505568](#) . Micro-Lock Plus Right Angle Header [505567](#)

Use With

Micro-Lock Plus Terminal [505431](#) . Micro-Lock Plus Pre-Crimped Leads [797581148](#) , [797581149](#) , [797582143](#) , [797582144](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION