

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0050841150](#)
Status: **Active**
Overview:
Description: 2.13mm Diameter MLX Power Crimp Housing Plug, 15 Circuits, Natural

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	42021
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Glow Wire Equivalent Part Number 366430008 . Current – Maximum per contact 20A if used with 36663 and 36664 terminal
Overview	mlx
Product Name	MLX
UPC	800753755291

Physical

Circuits (maximum)	15
Circuits Detail	15
Color - Resin	Natural
Flammability	94V-2
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	8.113/g
Number of Rows	5
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.35mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-55° to +105°C

Electrical

Current - Maximum per Contact	11.0A, 20.0A
-------------------------------	--------------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	42021-15A
--------------------	-----------

Reference - Drawing Numbers

Packaging Specification	PK-42021-XX-001
Product Specification	PS-42022-0001-001
Sales Drawing	SD-42021-XX-001
Test Summary	TS-42022-0001-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[42021](#) Series

Mates With

MLX Power Connector Header [42002](#) . MLX
Pin and Socket Receptacle [42022](#) . MLX
Power Connector Header [43255](#)

Use With

MLX Crimp Terminal [36663](#) , [36664](#) , [42023](#)
, [42024](#) . MLX Male Pre-Crimped Lead
[797582029](#) , [797582030](#) . MLX Female Pre-
Crimped Lead [797582031](#) , [797582032](#)