

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0532530270](#)
Status: **Active**
Overview: [Micro-Latch Wire-to-Board Connector System](#)
Description: 2.00mm Pitch, Micro-Latch PCB Header, Single Row, Vertical, Through Hole, Tin (Sn) Plating, 2 Circuits, Tray, 3.50mm PC Tail Length

Documents:	
3D Model	Product Specification 510651000-PS-000 (PDF)
Drawing (PDF)	Packaging Specification SPK-53253-001-001 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification 510650000-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification
UL E29179

General	
Product Family	PCB Headers
Series	53253
Application	Signal, Wire-to-Board
Overview	Micro-Latch Wire-to-Board Connector System
Product Name	Micro-Latch
UPC	756054354001

Physical	
Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	103.000/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.50mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical	
Current - Maximum per Contact	2.0A
Voltage - Maximum	125V



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - D(2020)9139-DC (19 Jan 2021) Halogen-Free Status Not Low-Halogen For more information, please visit Contact US	China RoHS China ROHS Green Image ELV Not Relevant RoHS Phthalates Not Contained

Search Parts in this Series
[53253](#) Series

Mates With
[51065](#) Crimp Housing, [50212](#) Crimp Terminal

Material Info

Reference - Drawing Numbers

Packaging Specification	SPK-53253-001-001
Product Specification	510650000-PS-000, 510651000-PS-000
Sales Drawing	532530000-SD-000

This document was generated on 08/17/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION