

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5601230300

Status:

Active

Overview:

DuraClik Connector System

Description:

DuraClik ISL Wire-to-Board Receptacle Housing, Single Row, White, 3 Circuits



Series image - Reference only

- Documents:
- Drawing (PDF)

3D Model (PDF)

3D Model

Product Specification PS-560123-001-001 (PDF)

Product Specification PS-560123-003-001 (PDF)

Application Specification AS-560123-001-001 (PDF)

Packaging Specification PK-560123-001-001 (PDF)

Test Summary 5601230400-TS (PDF)

Test Summary 5601230600-TS (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

|                |                                   |
|----------------|-----------------------------------|
| General        |                                   |
| Product Family | Crimp Housings                    |
| Series         | 560123                            |
| Application    | Automotive, Signal, Wire-to-Board |
| Overview       | DuraClik Connector System         |
| Product Name   | DuraClik                          |
| UPC            | 889056009539                      |

|                               |                |
|-------------------------------|----------------|
| Physical                      |                |
| Circuits (maximum)            | 3              |
| Color - Resin                 | White          |
| Gender                        | Receptacle     |
| Glow-Wire Capable             | No             |
| Keying to Mating Part         | None           |
| Lock to Mating Part           | Yes            |
| Material - Resin              | PBT            |
| Net Weight                    | 0.219/g        |
| Number of Rows                | 1              |
| Packaging Type                | Bag            |
| Panel Mount                   | No             |
| Pitch - Mating Interface      | 2.00mm         |
| Polarized to Mating Part      | Yes            |
| Stackable                     | No             |
| Temperature Range - Operating | -40° to +130°C |

|                             |     |
|-----------------------------|-----|
| Solder Process Data         |     |
| Lead-freeProcess Capability | N/A |

Material Info

|                             |                                      |
|-----------------------------|--------------------------------------|
| Reference - Drawing Numbers |                                      |
| Application Specification   | AS-560123-001-001                    |
| Packaging Specification     | PK-560123-001-001                    |
| Product Specification       | PS-560123-001-001, PS-560123-003-001 |
| Sales Drawing               | SD-560123-003-001                    |
| Test Summary                | 5601230400-TS, 5601230600-TS         |

EU ELV

Compliant

EU RoHS

Compliant

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

ELV

RoHS Phthalates

Green Image

Compliant

Not Contained

Search Parts in this Series  
560123 Series

Mates With  
DuraClik Right-Angle Header 502352 <br>DuraClik Vertical Header 560020

Use With  
DuraClik ISL Terminal 560124 <br>DuraClik ISL Retainer 5601250300 , 5601250301

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION