

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0731375003](#)
Status: **Active**
Overview: [BNC Miniature RF Connectors and Cable Assemblies](#)
Description: BNC 50 Ohm, Right-Angle PCB Bulkhead Jack Receptacle, Panel Isolated, Black PBT Housing, Housing Height 13.20mm, Nut and Lockwasher included

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification SD-73137-5003-PKG-00 \(PDF\)](#)

Agency Certification

CSA LR19980
UL E107635

General

Product Family RF/Coax Connectors
Series [73137](#)
Overview [BNC Miniature RF Connectors and Cable Assemblies](#)
Product Name BNC
Style PCB
Type Miniature
UPC 800753750258
Wire/Cable Type N/A

Physical

Cable Attachment N/A
Flammability 94V-0
Gender Jack
Keying to Mating Part None
Net Weight 15.347/g
Orientation Right Angle
PCB Mounting Through Hole
PCB Thickness - Recommended 3.20mm
Packaging Type Tray
Panel Mount Yes
Panel Mount Method Bulkhead

Electrical

Frequency 2 GHz
Impedance 50Ω
Power / Voltage VOLTAGE: 500 Vrms@Sea Level

Solder Process Data

Duration at Max. Process Temperature (seconds) 010
Lead-freeProcess Capability WAVE
Max. Cycles at Max. Process Temperature 001
Process Temperature max. C 245

Material Info

Reference - Drawing Numbers

Packaging Specification SD-73137-5003-PKG-00
Sales Drawing SD-73137-5003-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)
Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[73137 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION