

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0745460400](#)
Status: **Active**
Overview: [iPass Connector System](#)
Description: iPass PCIe x4 Cable Assembly, 28 AWG, 0.50m Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Cable Assemblies
Series [74546](#)
Assembly Configuration Dual Ended Connectors
Connector to Connector PCI Express-to-PCI Express
Overview [iPass Connector System](#)
Product Name iPass, PCI Express
Taxonomy High-Speed Pluggable I/O Cable
UPC 822350289658

Physical
Cable Length 0.50m
Circuits (Loaded) 38
Gender Plug/Plug
Lock to Mating Part Yes
Material - Metal Zinc Alloy
Net Weight 160.000/g
Number of Rows 2
Packaging Type Bag
Pitch - Mating Interface 0.80mm
Single Ended No
Waterproof / Dustproof Yes
Wire Insulation Diameter N/A
Wire Size AWG 28
Wire/Cable Type Round

Electrical
Current - Maximum per Contact 1.0A
Shield Type N/A
Shielded No
Voltage - Maximum 30V DC

Material Info

Reference - Drawing Numbers
Sales Drawing SD-74546-400-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Contained Per -
D(2022)4187-DC (10
June 2022)
C,C'-
azodi(formamide)
Halogen-Free
Status
Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[74546](#) Series

Mates With
[75586](#) iPass Receptacle

Use With
[74540](#) PCIe Guide Frame