

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0008500185

Status:

Active

Overview:

KK Interconnect Solutions

Description:

KK Trifurcon Crimp Terminal 7258, 22-26 AWG, Bag, Brass Tin (Sn)

Documents:

Drawing (PDF)

Product Specification PS-40-02-001 (PDF)

Packaging Specification PK-2759-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	7258
Application	Power
Crimp Quality Equipment	Yes
Overview	KK Interconnect Solutions
Packaging Alternative	08500183 (Reel)
Product Name	KK, Trifurcon
UPC	800753619135
Physical	
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.154/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.65mm max.
Wire Size AWG	22, 24, 26
Wire Size mm²	N/A

Solder Process Data	
Lead-freeProcess Capability	N/A

Material Info	
Engineering Number	7258-(P909)L

Reference - Drawing Numbers	
Packaging Specification	PK-2759-001-001
Product Specification	PS-40-02-001
Sales Drawing	SD-7258-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

7258 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals PremiumGrade Hand	11030016
Crimp Tool for KK 3.96mm Terminals, 22-26 AWG	638117400

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION