

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0009507081

Status:

Active

Overview:

KK Interconnect Systems

Description:

KK 3.96mm Crimp Terminal Housing, 8 Circuits, Natural

Documents:

Drawing (PDF)

3D Model (PDF)

3D Model

Product Specification PS-08-50-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Overview

Product Name

Taxonomy

UPC

Crimp Housings

2139

Power, Wire-to-Board

KK Interconnect Systems

KK 396

Connector Housings

800753531543

Physical

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Capable

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Temperature Range - Operating

8

Natural

94V-2

Receptacle

No

Nylon

2.048/g

1

Bag

No

3.96mm

See Product Specification

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

2139-8C

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-08-50-001

SD-2139-001, SD-2139-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

2139 Series

Mates With

KK 396 Headers: 41771 , 41772 , 41791 , 41792 , 42491 , 42492 , KK 396 Breakaway Headers: 41661 , 41662 , 41671 , 41672

Use With

2478 Crimp Terminals for 18-24 AWG, 2578 Crimp Terminals for 22-26 AWG

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION