

BU-20431-@ (Right-angle Banana Jack, Hook Plunger)



- The BU-20431 is an insulated, plug-on hook plunger with a standard, right-angle 4mm banana jack. Mounts to any test lead that uses shrouded, unshrouded, or retractable 4mm banana plugs.
- Overall length 4.6" (117mm), hook extension length = 0.41" (10mm)
- Material:

Housing	Nylon
Hook	Nickel-plated beryllium copper
Banana jack	Nickel-plated brass
Spring	Stainless-steel
- Rating:

Current	15 Amps
Voltage	1000V, CAT III
- Color: The "@" in the part number represents color.
Available colors: -0 Black, -2 Red, -6 Blue
- RoHS 3 compliant, CE Certified