

BU-40 Series

(Compact Insulated Battery Clip)





Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524

- The BU-40 series of clips are insulated compact battery clips.
- Overall length 2.3" (58mm), overall width 0.4" (10mm), overall height 1.8" (46mm), maximum jaw spread = 0.75" (19mm)
- Connects to wire up to 12 AWG via crimp or solder connection.
- Material:

BU-40A-@ Nickel-plated steel Nickel-plated copper BU-40C-@

Flexible PVC Insulators

Ratings:

BU-40A-@ Current: 15 Amps BU-40C-@ Current: 20 Amps

• The BU-40 is sold under the following models:

BU-40A-@ Nickel-plated steel clip BU-40C-@ Nickel-plated copper clip

• Color: The "@" in BU-40A-@ and BU-40C-@ represents insulator color.

Available colors: -0 Black, -2 Red

RoHS 3 compliant