


BU-P1296

(Adapter-BNC Male to Double Binding Post)



- Adapter-BNC Male to Double Binding Post
- Allows BNC female connector to be converted for use with standard 4mm test leads on 0.75" spacing.
- 0.16" (4.11mm) diameter holes in body give side stackable connections
- Material:
 - o BNC tarnish resistant plated brass body
 - Center Contact Gold plated brass
 - o Banana Jacks Nickel plated Brass
 - o Insulator Nylon housing
- Ratings:

o Impedance: 50 Ohms

o Hand-Held testing: 30VAC/60VDC Max.

o Hands free testing: 500 Vrms Max. (controlled)

• Color: The "@" in the model number indicates color.

Available colors are: -0 Black

RoHS 2 Compliant

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524