

BU-P3534

(BNC Right-angle Connector, Female-Male)



- Mueller's BU-P3534 is a BNC right-angle connector (Female-Male).
- Overall length 1.06" (27mm), overall width 1.02" (26mm)
- Material:

Body	Nickel-plated brass
Female contact	Gold-plated beryllium copper
Male contact	Gold-plated brass
Dielectric	PTFE
- Rating:

Voltage	30VAC/60VDC Max, 500VRMS Max.
Temperature	-65°C (-85°F) to 165°C (329°F)
Impedance	50 Ohms
- RoHS 3 compliant