

BU-P3750-@
(Gold-plated Binding Post, Panel Mount)



- The BU-P3750 is a panel mountable gold-plated binding post that accepts unshrouded or retractable 4mm banana plugs, bare wire, or spade lugs.
- Overall length 1.78" (45.2mm), OD = 0.44" (11.2mm)
- Mounting:
 - Mount thru panels between 0.70" and 0.25" thick with a $\varnothing 0.375$ " (9.52mm) hole.
 - Pole Threads: 8-32 threads
- Material: Contacts Gold-plated brass
 Insulators Polycarbonate
- Rating: Current 15 Amps
 Voltage Hands-free testing up to 2500 VRMS
 Temperature -50°C to 115°C
- Color: The "@" in the model number indicates color.
 Available colors are: -0 Black, -2 Red
- RoHS 3 compliant, exemption 6c