

BU-P4543-@**(Double Pin Tip Jack)**

- The BU-P4543 is a double pin tip jack. Can be mounted to panels up to 0.25" thick.
- Material: Body Nylon
 Contacts Gold-plated beryllium copper
- Overall length 0.88" (22.35mm), overall width 0.86" (21.84mm)
 - Pole Threads: 8-32
- Mounting:
 - Mount thru panels up to 0.25" (6.35mm) thick. Recommended panel cutout is 2X Ø0.25" (6.35mm) holes spaces 0.50" (12.7mm) apart center-to-center.
- Ratings:
 - Amperage: 5 Amps
 - Voltage: Hands-free testing to 1500 VRMS
 - Temperature: -50°C to 120°C
- Color: The "@" in the model number indicates color.
 Available colors are: -0 Black, -2 Red
- RoHS compliant