

BU-PMDP-@

(Solderless, Stackable Double Banana Plug with Cable Guide)



- The BU-PMDP is a double 4mm banana plug with industry standard 0.75" center-to-center plug spacing. Wires can be attached by the axial setscrews and there is a small compartment between the banana plugs which can hold small components.
- Overall length 1.58" (40.13mm), banana jack spacing = 0.75" (19.05mm)
- Material: Banana plug Nickel-plated beryllium copper
 Body Polypropylene
- Rating:
 - Current: 15 Amps
 - Voltage: Hands-free testing to 1500V CAT I
- Color: The "@" in the model number indicates color.
 Available colors are: -0 Black, -2 Red, -5 Green, -9 White
- RoHS 3 Compliant