

WI-M-10-XX-@

(Extra Heavy-Duty 10 AWG, UL Recognized, Silicone Jacket Test Lead Wire)



- Mueller's WI-M-10-@ is 10 AWG, 1050/0.08 stranded, tinned copper wire with highly flexible 6mm diameter silicone jacket.

- Ratings:

Voltage	1100V
Dielectric Strength	3.2 KV/Min
Spark Test	10 KV
Rated Temperature	-40°C to 180°C
Temperature Rating	FT2
UL Recognized	UL 3640

- Length: The "XX" in the model number indicated length in feet.
Standard lengths: 10', 25', 30', 50', and 100'
- Color: The "@" in the model number represents color.
Available colors: -0 Black, -2 Red