

WI-M-18-XX-@
(18 AWG, Silicone Jacket Test Lead Wire)



- Mueller's WI-M-18 is an 18 AWG, 413/44 strand (7/59/.05mm) copper wire with a highly flexible, 0.140" (3.6mm) diameter silicone jacket.
- UL listed: Style 3577
- Ratings: Current 22 Amps @ 150°C
 Voltage 3000V
- Length: The "XX" in the model number indicates length in feet. Standard lengths: 10', 25' (custom lengths available upon request)
- Color: The "@" in the model number represents color. Available colors:
 -0 Black, -2 Red
- RoHS 3 compliant