

MODLINK MSDD SOCKET INSERT GERMANY

250VAC/16A with LED yellow

Germany (VDE) white
Screw terminals
LED (yellow)

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
customs tariff number	85366990
GTIN	4048879038294
Packaging unit	1
Mechanical data Mounting data	
Height	88 mm
Width	51 mm
Depth	68 mm
Environmental characteristics Climatic	
Storage temperature min.	-30 °C
Storage temperature max.	60 °C
Germany (VDE)	
Connection cross section max.	6 mm²

AWG number max.	10
Operating voltage AC	250 V
Operating current	16 A
Status indication LED	yellow
Connection	Screw terminals SK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes