

MODLINK MSDD SINGLE COMBI INSERT GERMANY

2x data cutout

1× Germany (VDE) white

2× RJ45 cut-out

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
customs tariff number	85366990
GTIN	4048879593427
Packaging unit	1

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Mechanical data | Mounting data

Height	87,5 mm
Width	50,7 mm
Depth	43 mm

Environmental characteristics | Climatic

Operating temperature min.	-5 °C
Operating temperature max.	50 °C

Storage temperature min.	-10 °C
--------------------------	--------

Storage temperature max.	60 °C
--------------------------	-------

Shielding plate

Connection information	Threaded hole M4
------------------------	------------------

Tightening torque	0,9 Nm
-------------------	--------

Germany (VDE)

Connection cross section max.	2,5 mm²
-------------------------------	---------

AWG number max.	14
-----------------	----

Operating voltage AC	250 V
----------------------	-------

Operating current	16 A
-------------------	------

Connection	Spring clamp terminals FK
------------	---------------------------

No. of poles	2 + PE
--------------	--------

Connections per pole	2
----------------------	---

Protection contact present	yes
----------------------------	-----