

Thermal transfer printer - THERMOMARK ROLL 2.0 - 1085260

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

Product Description

The THERMOMARK ROLL 2.0 prints markers in roll format for top quality terminal, wire, cable, equipment, and plant marking applications. You can easily create high-quality printed labels and markers.

Your advantages

- ✓ The THERMOMARK ROLL 2.0 prints marking material in roll format. For applications in terminal, wire, cable, equipment, and plant marking
- ✓ Printing of punched and continuous adhesive labels, insert labels, and shrink sleeves
- ✓ Fast, high-quality, and durable printing
- ✓ Easy and intuitive operation via touch color display
- ✓ Maintenance-free operation with proven thermal transfer printer technology
- ✓ Easy to control with the PROJECT COMPLETE software
- ✓ USB and Ethernet connections



Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 834764
GTIN	4055626834764
Weight per Piece (excluding packing)	5,500.000 g
Weight per piece (including packing)	6,370.000 g
Custom tariff number	84433210
Country of origin	Germany
Sales Key	N1 - Printer+Autom.Tools

Technical data

General

Interfaces	10/100 Mbps Ethernet, USB 2.0, RS-232
------------	---------------------------------------

Thermal transfer printer - THERMOMARK ROLL 2.0 - 1085260

Technical data

General

Weight	3.8 kg
--------	--------

Dimensions

Length	320 mm
Height	189 mm
Width	240 mm

Connection data

Minimum voltage	100 V AC
Max. voltage	240 V AC
Additional text	50 Hz ... 60 Hz

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 10;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	19140104
eCl@ss 11.0	19140104
eCl@ss 4.0	24190103
eCl@ss 4.1	24190103
eCl@ss 5.0	19020205
eCl@ss 5.1	19020205
eCl@ss 6.0	19140100
eCl@ss 7.0	19140104
eCl@ss 9.0	19140104

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001694
ETIM 6.0	EC001672
ETIM 7.0	EC001672

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107

Thermal transfer printer - THERMOMARK ROLL 2.0 - 1085260

Classifications

UNSPSC

UNSPSC 13.2	43212107
UNSPSC 18.0	43212108
UNSPSC 19.0	43212108
UNSPSC 20.0	43212108
UNSPSC 21.0	43212108

Approvals

Approvals

Approvals

CCC / KC / EAC-RoHS / EAC

Ex Approvals

Approval details

CCC		2019010904194065
-----	---	------------------

KC		http://eng.kcc.go.kr/user/ehpMain.do	R-R-YG3-TR20
----	---	---	--------------

EAC-RoHS		RU D- DE.HB49.B.00023
----------	---	--------------------------

EAC		RU D- DE.GB09.B.00141
-----	---	--------------------------

Accessories

Accessories

Documentation

Thermal transfer printer - THERMOMARK ROLL 2.0 - 1085260

Accessories

Manual - UM IA THERMOMARK ROLL - 2910897



Manual

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM..., width: 110 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 110 BU - 0829544



Ink ribbon, width: 110 mm, color: blue

Ink ribbon - THERMOMARK-RIBBON 110 GN - 0829542



Ink ribbon, width: 110 mm, color: green

Ink ribbon - THERMOMARK-RIBBON 110 RD - 0829543



Ink ribbon, width: 110 mm, color: red

Thermal transfer printer - THERMOMARK ROLL 2.0 - 1085260

Accessories

Ink ribbon - THERMOMARK-RIBBON 110-EML-HT - 0800342



Ink ribbon, for roll printer for printing product group EML-HT..., width: 110 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 110-WMSU - 0801358



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 110 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 110-WMSU WH - 0801359



Ink ribbon, for roll printer for printing product group WMS... (black), width: 110 mm, color: white

Ink ribbon - THERMOMARK-RIBBON 64-WMSU - 0801360



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 64 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 64-WMSU WH - 0801361



Ink ribbon, for roll printer for printing product group WMS... (black), width: 64 mm, color: white

Thermal transfer printer - THERMOMARK ROLL 2.0 - 1085260

Accessories

Ink ribbon - THERMOMARK-RIBBON 110-WMTB HF - 5148007



Ink ribbon, for roll printer for printing product groups WMTB HF..., WMS-2 HF..., TMT..., EMT..., EMLF..., PML-..., width: 110 mm, color: black

Mounting material

Original packaging - TC/TR-PACKAGE WITH FOAM - 0801804



Original packaging for transportation

Locking - TR-MARGIN STOP - 0801810



Locking

Pressure roller - TR-PRESSURE ROLLER DR4-50 - 0801800

Pressure roller



Pressure roller - TR-PRESSURE ROLLER STANDARD - 0801802

Pressure roller



Thermal transfer printer - THERMOMARK ROLL 2.0 - 1085260

Accessories

Demolition plate - TR-TEAR OFF PLATE - 0801803



Demolition plate

Planning and marking software

Software - PROJECT COMPLETE - 1050453



Intuitive planning and marking software for configuring terminal strips and for professional marking of marking materials for terminal blocks, conductors, cables, devices, and systems. The software is available for download

Printing system accessories

Cutter - THERMOMARK ROLL-CUTTER - 5146422



Cutter for THERMOMARK ROLL and THERMOMARK ROLL 2.0, cutter width: 110 mm, suitable for: TML, SK, EML-RM, PMM, WMS, WMS-2 HF, WMS-OT HF, TMT continuous media, and EMT (EX15)R

Cutter - THERMOMARK ROLL-CUTTER/P - 5146435



Perforation cutter, for the THERMOMARK ROLL and THERMOMARK ROLL 2.0, cutter width: 45 mm, suitable for: WMS continuous media up to 25.4 mm, WMS-2 continuous media up to 25.4 mm, WMS-OT HF continuous media, TMT continuous media, and EMT (EX15)R

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm

Thermal transfer printer - THERMOMARK ROLL 2.0 - 1085260

Accessories

Media hub - THERMOMARK-ERH 500 - 5146309



External media hub, for the THERMOMARK ROLL, for roll diameter of up to 500 mm

Transport case - TL CASE - 0800613



Transport case for THERMOMARK printer, rounded profile case with aluminum frame

Cart for printer - TL CASE TROLLY - 0803337



Trolley for the transport cases for THERMOMARK LINE and THERMOMARK ROLL X1

Accessories - THERMOMARK-CP - 5145371



Cleaning pen, for thermal transfer printers
