

Housing set - UM-PRO-KIT-B122-L180-7035 - 1310989


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Profile housing (PA), mounting type: DIN rail mounting, color: light gray (7035), dimensions on the DIN rail: width: 183.8 mm, height: 142.3 mm, depth: 39.45 mm, incl. 2 lateral elements (PA), color: black (9005), for PCBs with width: 122 mm, length: 180 mm, PCB surface: 19240 mm²



Key Commercial Data

| | |
|----------------------|---|
| Packing unit | 1 pc |
| GTIN |  4 063151 571023 |
| GTIN | 4063151571023 |
| Custom tariff number | 39169010 |

Technical data

Product properties

| | |
|---------------------------|---------------------------|
| Brief article description | Housing set |
| Type | UM-PRO-KIT-B122-L180-7035 |
| Item no. | 1310989 |
| Housing type | Profile housing |
| Housing series | UM-PRO |
| Type | incl. 2 lateral elements |
| Mounting type | DIN rail mounting |

Dimensions

| | |
|---------------------------------|----------|
| Width | 183.8 mm |
| Height | 142.3 mm |
| Depth | 39.45 mm |
| Depth from top edge of DIN rail | 32.45 mm |

PCB specifications

| | |
|-----------------------|----------------------------------|
| Number of PCB holders | 3 |
| Dimensions | 122 mm x 180 mm (PCB dimensions) |

Housing set - UM-PRO-KIT-B122-L180-7035 - 1310989

Technical data

PCB specifications

| | |
|----------------------|---|
| PCB surface, maximum | 19240 mm ² |
| PCB thickness | 1.4 mm ... 1.8 mm |
| Mounting position | parallel to the DIN rail |
| Type of PCB mount | Insertion/securing with additional elements |

Material specifications - Profile

| | |
|--|-------------------|
| Material | PA |
| Color (RAL) | light gray (7035) |
| Flammability rating according to UL 94 | V0 |

Material specifications - Lateral elements

| | |
|--|--------------|
| Material | PA |
| Color (RAL) | black (9005) |
| Flammability rating according to UL 94 | V0 |

Ambient conditions

| | |
|---|--|
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Relative humidity (storage/transport) | 80 % |

General information

| | |
|--------------|--|
| Type of note | Assembly instruction: |
| Note | Please observe the assembly instructions available in the download area. |

Packaging specifications

| | |
|----------------------------|---------------------|
| Type of packaging | packed in cardboard |
| Pieces per package | 1 |
| Denomination packing units | Pcs. |
| Outer packaging type | Carton |

Classifications

eCl@ss

| | |
|-------------|----------|
| eCl@ss 11.0 | 27182701 |
|-------------|----------|

Approvals

Approvals

Approvals

UL Recognized

Housing set - UM-PRO-KIT-B122-L180-7035 - 1310989

Approvals

Ex Approvals

Approval details

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

FILE E 240868