

## Housing set - UM-PRO-KIT-B122-L200-7035 - 1310990


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Profile housing (PA), mounting type: DIN rail mounting, color: light gray (7035), dimensions on the DIN rail: width: 203.8 mm, height: 142.3 mm, depth: 39.45 mm, incl. 2 lateral elements (PA), color: black (9005), for PCBs with width: 122 mm, length: 200 mm, PCB surface: 21590 mm<sup>2</sup>



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 063151 570422
GTIN	4063151570422
Custom tariff number	39169010

### Technical data

#### Product properties

Brief article description	Housing set
Type	UM-PRO-KIT-B122-L200-7035
Item no.	1310990
Housing type	Profile housing
Housing series	UM-PRO
Type	incl. 2 lateral elements
Mounting type	DIN rail mounting

#### Dimensions

Width	203.8 mm
Height	142.3 mm
Depth	39.45 mm
Depth from top edge of DIN rail	32.45 mm

#### PCB specifications

Number of PCB holders	3
Dimensions	122 mm x 200 mm (PCB dimensions)

# Housing set - UM-PRO-KIT-B122-L200-7035 - 1310990

## Technical data

### PCB specifications

PCB surface, maximum	21590 mm <sup>2</sup>
PCB thickness	1.4 mm ... 1.8 mm
Mounting position	parallel to the DIN rail
Type of PCB mount	Insertion/securing with additional elements

### Material specifications - Profile

Material	PA
Color (RAL)	light gray (7035)
Flammability rating according to UL 94	V0

### Material specifications - Lateral elements

Material	PA
Color (RAL)	black (9005)
Flammability rating according to UL 94	V0

### Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Relative humidity (storage/transport)	80 %

### General information

Type of note	Assembly instruction:
Note	Please observe the assembly instructions available in the download area.

### Packaging specifications

Type of packaging	packed in cardboard
Pieces per package	1
Denomination packing units	Pcs.
Outer packaging type	Carton

## Classifications

eCl@ss

eCl@ss 11.0	27182701
-------------	----------

## Approvals

Approvals

Approvals

UL Recognized

## Housing set - UM-PRO-KIT-B122-L200-7035 - 1310990

### Approvals

Ex Approvals

---

#### Approval details

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

FILE E 240868