


TECHNICAL DATA SHEET


www.quadrios.de


Version 1.0_012020


Micro USB 3.0 Male Connector modular

Item No. 2001C212









Note:Tx and Rx are defined from the device perspective





Material: Housing: PP Insulator: PBT

Connector shell: SPCC with plated Ni 40µ min.

Contact: Brass with plated Au1µ

Technical:

Voltage rating: 100V max. Current rating: 1.8A max.

Contact resistance: $50m\Omega$ max. Insulation resistance: $1000M\Omega$ min.

Dielectric withstanding voltage: 500V/AC(R.M.S)

Operation temperature: -40 ~85°C