


## Heat shrink solder seal sleeve connector (2:1) White 0,25 ~ 0,34 mm<sup>2</sup>



Picture	Color	QTY	Cable Size		Size (mm)	
			AWG	mm <sup>2</sup>	Diameter	Length
	White	20 pcs	26 ~ 24	0,25 ~ 0,34	1.7	26

- Type: Heat shrink solder sleeve 2011C398
- Color: White / Red / Blue / Yellow
- Waterproof when used correctly
- Minimum fully insulated temperature: 80 °C
- Fully melt temperature of solder: 160 °C
- Minimum melt temperature of solder: 138 °C
- Shrinkage temperature: 138 °C ~ 160 °C
- Voltage resistance: 600 V
- Working temperature: -55 °C ~ 125 °C

Notice: Max. current limited by cable-diameter, cable-material and quality of the soldering joint!  
Connection only by qualified electricians. We assume no liability or warranty in case of incorrect application.