

Wire ferrules assortment 22C484

0.5 mm² ... 6 mm²


500 pcs set



RoHS



REACH
Compliant



Quadrios wire end ferrules guarantee optimal crimp connections in conjunction with fitting crimping tools. This set includes uninsulated wire end ferrules for maximum flexibility. The ferrules are especially suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs. Optimal for use with suitable Quadrios wire end ferrule crimping pliers. Refill packs available – see table down below.

Technical data: Voltage (max.): 440 V, Material: copper • Plating: tin • Type: uninsulated / without plastic collar • Content: 100x 0.5 mm², barrel-length 8 mm • 100x 0.75 mm², barrel-length 8 mm • 100x 1.0 mm², barrel-length 8 mm • 100x 1.5 mm², barrel-length 8 mm • 50x 2.5 mm², barrel-length 8 mm • 25x 4.0 mm², barrel-length 8 mm • 25x 6.0 mm², barrel-length 8 mm.



Substitute ferrules in 100 pcs units are available:

Part No.	Description	Cross-section	Bezel diameter	Inner diameter	Outer diameter	Barrel length	EAN	Content
22C471	Ferrules, uninsulated 0.25 mm ²	0.25 mm ²	1.5 mm	0.8 mm	1.1 mm	6 mm	4260732282709	100 pcs
22C472	Ferrules, uninsulated 0.34 mm ²	0.34 mm ²	1.5 mm	0.8 mm	1.1 mm	6 mm	4260732282716	100 pcs
22C473	Ferrules, uninsulated 0.5 mm ²	0.5 mm ²	1.7 mm	1 mm	1.3 mm	6 mm	4260732282723	100 pcs
22C474	Ferrules, uninsulated 0.75 mm ²	0.75 mm ²	1.9 mm	1.2 mm	1.5 mm	6 mm	4260732282730	100 pcs
22C475	Ferrules, uninsulated 1 mm ²	1 mm ²	2.2 mm	1.4 mm	1.7 mm	6 mm	4260732282747	100 pcs
22C476	Ferrules, uninsulated 1.5 mm ²	1.5 mm ²	2.5 mm	1.7 mm	2 mm	8 mm	4260732282754	100 pcs
22C477	Ferrules, uninsulated 2.5 mm ²	2.5 mm ²	3.3 mm	2.3 mm	2.6 mm	8 mm	4260732282761	100 pcs
22C478	Ferrules, uninsulated 4 mm ²	4 mm ²	3.9 mm	2.8 mm	3.2 mm	12 mm	4260732282778	100 pcs
22C479	Ferrules, uninsulated 6 mm ²	6 mm ²	4.7 mm	3.5 mm	3.9 mm	12 mm	4260732282785	100 pcs
22C480	Ferrules, uninsulated 10 mm ²	10 mm ²	5.8 mm	4.5 mm	4.9 mm	12 mm	4260732282792	100 pcs
22C481	Ferrules, uninsulated 16 mm ²	16 mm ²	7.2 mm	5.8 mm	6.2 mm	12 mm	4260732282808	100 pcs

Connection only by qualified electricians!