

Heat shrink butt crimp connectors with glue

Item No. 23C494 (45 pcs.)

Item No. 23C495 (50 pcs.)



Technical data: Shrink ratio: 3 : 1 • IP-Class: IP 67 • Temp.-range: -55 °C ... 125 °C • Voltage resistance: max. 600 V • Shrink temperature: 80 °C ... 130 °C • Glue melts during shrink-process.

Only three steps required for installation: 1. select diameter 2. crimp 3. shrink with hot air source
Connection only by qualified electricians! We assume no liability or warranty in case of incorrect application.

Item No.: 23C494 (45 pcs. Set)

Color	Cable size mm ²	Cable size AWG	Diameter	Length	Max. current	Content
Red	0.5 ... 1.5 mm ²	22 ... 16	4.7 mm	36 mm	19 A	15 pcs.
Blue	1.5 ... 2.5 mm ²	16 ... 14	5.7 mm	37 mm	27 A	12 pcs.
Black	2.5 ... 4.0 mm ²	14 ... 12	6.0 mm	38 mm	35 A	10 pcs.
Yellow	4.0 ... 6.0 mm ²	12 ... 10	6.9 mm	42 mm	48 A	8 pcs.

Item No.: 23C495 (50 pcs. Set)

Color	Cable size mm ²	Cable size AWG	Diameter	Length	Max. current	Content
White	0.3 ... 0.5 mm ²	26 ... 24	4.0 mm	26 mm	9 A	20 pcs.
Red	0.5 ... 1.5 mm ²	22 ... 16	4.7 mm	36 mm	19 A	10 pcs.
Blue	1.5 ... 2.5 mm ²	16 ... 14	5.7 mm	37 mm	27 A	10 pcs.
Black	2.5 ... 4.0 mm ²	14 ... 12	6.0 mm	38 mm	35 A	10 pcs.

Refill-packs available:

Item No.	Cable size mm ²	Color	Diameter	Current max.	EAN / GTIN	Content
22C465	4 ... 6 mm ²	Yellow	6.9 mm	48 A	4260732281559	80 pcs.
22C466	1.5 ... 2.5 mm ²	Blue	5.7 mm	27 A	4260732281566	150 pcs.
22C467	0.5 ... 1.5 mm ²	Red	4.7 mm	19 A	4260732281573	150 pcs.
22C468	2.5 ... 4 mm ²	Black	6 mm	35 A	4260732281580	80 pcs.
22C469	0.3 ... 0.5 mm ²	White	4 mm	9 A	4260732281597	150 pcs.