

Ferrule assortment 1200 pcs (DIN color code) with Crimping Pliers Bundle-Item-No.: 24C531

These ferrules are especially suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs.

The assortment contains a 1200-piece premium ferrule set (DIN color code) for an application range of cable cross sections from 0.5 to 10 mm².

The included crimping tool is optimally matched to the field of application and has an automatic adjustment to the sleeve diameters between 0.25 and 10 mm². The square crimping claw ensures a safe crimping process, the ergonomic full-shell-handle fits well in the hand and allows comfortable working. The pliers have an adjustment option for fine adjustment of the compressive force and a quick locking safety lock



Technical Specifications

Voltage (max.): 440 V • Material: polyamide, copper alloy, tin-plated. The ferrules comply with RoHS directives and are CE compliant. Installation by qualified electricians only.

Content

Practical assortment box • 25 ferrules yellow 6 mm² (10 AWG) • 25 ferrules red 10 mm² (7 AWG) • 50 ferrules grey 4 mm² (12 AWG) • 250 ferrules blue 2,5 mm² (14 AWG) • 250 ferrules black 1.5 mm² (16 AWG) • 200 ferrules grey 0.75 mm² (20 AWG) • 200 ferrules red 1 mm² (18 AWG) • 200 ferrules white 0.5 mm² (22 AWG) • Crimping tool with four-mandrel press claw and automatic adjustment (fine adjustment ratchet pressure) Crimping-range from 0.25 to 10 mm² (AWG 23 ... 7).