

Multifunction Wire-Stripper AWG

Item-No.: 24T063

These multifunctional wire stripper combines various functions in one tool: stripping, crimping, cutting and gripping. Made from robust tool steel, the pliers are ideal for fine work, with a lever arm thickness of just 4.3 mm. The comfortable red plastic handle sits comfortably in the users hand. Weighing just 153 g and with compact dimensions, the pliers are very easy to handle and light enough to work with for long periods at a time. The serrated gripping surface has a length of 7 mm. The crimping range of the slots for insulated and non-insulated cable lugs is 12 ... 20 AWG (0.75 ... 4 mm²). The cutting blade under the joint is 11 mm long. Six slots for stripping stranded wires and wires are available in a range of 10 ... 20 AWG (0.75 ... 6 mm²).



Technical Specifications

Length of the tool appx. 174 mm • Weight: appx. 153 g.

| Value AWG | Value metric |
|-----------|----------------------|
| AWG 20 | 0,75 mm ² |
| AWG 18 | 1,00 mm ² |
| AWG 16 | 1,50 mm ² |
| AWG 14 | 2,50 mm ² |
| AWG 12 | 4,00 mm ² |
| AWG 10 | 6,00 mm ² |

Application by qualified electricians only.

